



MAGGIO 2013

MAY 2013

MAI 2013

MAI 2013

MAYO 2013

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Description |
|-----|--------------------|--|---------------------------------------|---------------------------------------|--|---|
| 1 | 92810062 | Assieme porta - RF430 - RF630 | Door unit - RF430 - RF630 | Türensatz - RF430 - RF630 | Ensemble porte - RF430 - RF630 | Conjunto de puerta - RF430 - RF630 |
| 1 | 92710301 | Assieme porta - RF630L - RF930 | Door unit - RF630L - RF930 | Türensatz - RF630L - RF930 | Ensemble porte - RF630L - RF930 | Conjunto de puerta - RF630L - RF930 |
| 1 | 92810063 | Assieme porta - RF435 - RF635 | Door unit - RF435 - RF635 | Türensatz - RF435 - RF635 | Ensemble porte - RF435 - RF635 | Conjunto de puerta - RF435 - RF635 |
| 1 | 92710311 | Assieme porta - RF635L - RF935 | Door unit - RF635L - RF935 | Türensatz - RF635L - RF935 | Ensemble porte - RF635L - RF935 | Conjunto de puerta - RF635L - RF935 |
| 2 | 92820162 | Guarnizione vetro - RF430 - RF630 | Glass gasket - RF430 - RF630 | Scheibendichtung - RF430 - RF630 | Joint vitre - RF430 - RF630 | Junta del cristal - RF430 - RF630 |
| 2 | 92720261 | Guarnizione vetro - RF630L - RF930 | Glass gasket - RF630L - RF930 | Scheibendichtung - RF630L - RF930 | Joint vitre - RF630L - RF930 | Junta del cristal - RF630L - RF930 |
| 2 | 92820163 | Guarnizione vetro - RF435 - RF635 | Glass gasket - RF435 - RF635 | Scheibendichtung - RF435 - RF635 | Joint vitre - RF435 - RF635 | Junta del cristal - RF435 - RF635 |
| 2 | 92720271 | Guarnizione vetro - RF635L - RF935 | Glass gasket - RF635L - RF935 | Scheibendichtung - RF635L - RF935 | Joint vitre - RF635L - RF935 | Junta del cristal - RF635L - RF935 |
| 3 | 91610001 | Vetro porta - RF430 - RF630 - 626X93 | Door glass - RF430 - RF630 - 626X93 | Türscheibe - RF430 - RF630 - 626X93 | Vitre porte - RF430 - RF630 - 626X93 | Cristal de la puerta - RF430 - RF630 - 626X93 |
| 3 | 91610008 | Vetro porta - RF630L - RF930 - 936X93 | Door glass - RF630L - RF930 - 936X93 | Türscheibe - RF630L - RF930 - 936X93 | Vitre porte - RF630L - RF930 - 936X93 | Cristal de la puerta - RF630L - RF930 - 936X93 |
| 3 | 91610003 | Vetro porta - RF435 - RF635 - 726X93 | Door glass - RF435 - RF635 - 726X93 | Türscheibe - RF435 - RF635 - 726X93 | Vitre porte - RF435 - RF635 - 726X93 | Cristal de la puerta - RF435 - RF635 - 726X93 |
| 3 | 91610007 | Vetro porta - RF635L - RF935 - 1086X93 | Door glass - RF635L - RF935 - 1086X93 | Türscheibe - RF635L - RF935 - 1086X93 | Vitre porte - RF635L - RF935 - 1086X93 | Cristal de la puerta - RF635L - RF935 - 1086X93 |
| 4 | 92820132 | Struttura porta - RF430 - RF630 | Door structure - RF430 - RF630 | Türrahmen - RF430 - RF630 | Structure porte - RF430 - RF630 | Estructura de la puerta - RF430 - RF630 |
| 4 | 92720221 | Struttura porta - RF630L - RF930 | Door structure - RF630L - RF930 | Türrahmen - RF630L - RF930 | Structure porte - RF630L - RF930 | Estructura de la puerta - RF630L - RF930 |
| 4 | 92820133 | Struttura porta - RF435 - RF635 | Door structure - RF435 - RF635 | Türrahmen - RF435 - RF635 | Structure porte - RF435 - RF635 | Estructura de la puerta - RF435 - RF635 |
| 4 | 92720231 | Struttura porta - RF635L - RF935 | Door structure - RF635L - RF935 | Türrahmen - RF635L - RF935 | Structure porte - RF635L - RF935 | Estructura de la puerta - RF635L - RF935 |

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Descríp |
|-----|--------------------|-------------------------------------|---------------------------------------|----------------------------------|---------------------------------------|-------------------------------------|
| 5 | 91510011 | Manopola | Knob | Drehknopf | Manette | Mango |
| 6 | 91110007 | Vite inox TBE M12x30 | St. steel TBE M12x30 screws | Schraube Edelstahl TBE M12x30 | Vis inox TBE M12x30 | Tornillo inox TBE M |
| 7 | 92820152 | Profilo fermavetro - RF430 - RF630 | Glazing bead profile - RF430 - RF630 | Glashalteprofil - RF430 - RF630 | Profil blocage vitre - RF430 - RF630 | Perfil de sujeción - RF430 - RF630 |
| 7 | 92720241 | Profilo fermavetro - RF630L - RF930 | Glazing bead profile - RF630L - RF930 | Glashalteprofil - RF630L - RF930 | Profil blocage vitre - RF630L - RF930 | Perfil de sujeción - RF630L - RF930 |
| 7 | 92820153 | Profilo fermavetro - RF435 - RF635 | Glazing bead profile - RF435 - RF635 | Glashalteprofil - RF435 - RF635 | Profil blocage vitre - RF435 - RF635 | Perfil de sujeción - RF435 - RF635 |
| 7 | 92720251 | Profilo fermavetro - RF635L - RF935 | Glazing bead profile - RF635L - RF935 | Glashalteprofil - RF635L - RF935 | Profil blocage vitre - RF635L - RF935 | Perfil de sujeción - RF635L - RF935 |
| 8 | 92810150 | Ghiera camino | Flue ring nut | Schraubring Dampfblass | Bague sortie de fumée | Anillo chimenea |
| 9 | 92710180 | Colonna sx RF 1/E | Left column RF 1/E | Linke Säule RF 1/E | Colonne gauche RF 1/E | Columna izda. RF |
| 9 | 92710190 | Colonna sx RF 2/E | Left column RF 2/E | Linke Säule RF 2/E | Colonne gauche RF 2/E | Columna izda. RF |
| 10 | 92710220 | Banco - RF430 - RF630 | Counter - RF430 - RF630 | Bank - RF430 - RF630 | Banc - RF430 - RF630 | Barra - RF430 - RF |
| 10 | 92710230 | Banco - RF630L - RF930 | Counter - RF630L - RF930 | Bank - RF630L - RF930 | Banc - RF630L - RF930 | Barra - RF630L - F |
| 10 | 92710240 | Banco - RF435 - RF635 | Counter - RF435 - RF635 | Bank - RF435 - RF635 | Banc - RF435 - RF635 | Barra - RF435 - RF |
| 10 | 92710250 | Banco - RF635L - RF935 | Counter - RF635L - RF935 | Bank - RF635L - RF935 | Banc - RF635L - RF935 | Barra - RF635L - F |
| 11 | 92710205 | Colonna dx RF 1/E | Right column RF 1/E | Rechte Säule RF 1/E | Colonne droite RF 1/E | Columna dcha. RF |
| 11 | 92710215 | Colonna dx RF 2/E | Right column RF 2/E | Rechte Säule RF 2/E | Colonne droite RF 2/E | Columna dcha. RF |
| 12 | 91611620 | Frontale comandi RF 1/E | Control panel front RF 1/E | Frontblende RF 1/E | Bandeau de commande RF 1/E | Frontal de mandos |
| 12 | 91611630 | Frontale comandi RF 2/E | Control panel front RF 2/E | Frontblende RF 2/E | Bandeau de commande RF 2/E | Frontal de mandos |
| 13 | 91310212 | Sonda TCJ | TCJ probe | Sonde TCJ | Sonde TCJ | Sonda TCJ |
| 14 | 91310261 | Scheda di controllo | Control board | Kontrollkarte | Carte de contrôle | Tarjeta de control |
| 15 | 91310231 | Morsettiera | Terminal board | Klemmenbrett | Bornier | Regleta de bornes |
| 17 | 91310051 | Termostato di sicurezza | Safety thermostat | Sicherheitsthermostat | Thermostat de sécurité | Termostato de seg |
| 18 | 91310136 | Contattore | Contacteur | Schütz | Compteur | Contacteur |

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Descrizione |
|-----|--------------------------|---|---|--|---|--|
| 19 | 91310511 | Portafusibile | Fuse box | Sicherungshalterung | Porte-fusible | Portafusibile |
| 20 | 91310502 | Fusibile | Fuse | Sicherung | Fusible | Fusibile |
| 22 | 91510223 | Pressacavo | Cable gland | Zugentlastung | Serre-câble | Sujetacable |
| 23 | 91610130 | Mattoni refrattario - RF430 RF630L 308X616 | Firebrick - RF430 - RF630L 308X616 | Schamottestein - RF430 - RF630L 308X616 | Brique réfractaire - RF430 - RF630L 308X616 | Ladrillo refractario RF630L 308X616 |
| 23 | 91610131 | Mattoni refrattario - RF630 RF930 308X924 | Firebrick - RF630 - RF930 308X924 | Schamottestein - RF630 - RF930 308X924 | Brique réfractaire - RF630 - RF930 308X924 | Ladrillo refractario RF930 308X924 |
| 23 | 91610140 | Mattoni refrattario - RF435 RF635L 358X716 | Firebrick - RF435 - RF635L 358X716 | Schamottestein - RF435 - RF635L 358X716 | Brique réfractaire - RF435 - RF635L 358X716 | Ladrillo refractario RF635L 358X716 |
| 23 | 91610141 | Mattoni refrattario - RF635 RF935 358X1074 | Firebrick - RF635 - RF935 358X1074 | Schamottestein - RF635 - RF935 358X1074 | Brique réfractaire - RF635 - RF935 358X1074 | Ladrillo refractario RF935 358X1074 |
| 24 | 92710040 | Profilo fermapietre - RF430 RF630 | Glazing bead profile - RF430 RF630 | Steinhalteprofil - RF430 RF630 | Profil de blocage des pierres RF430 - RF630 | Perfil sujeción pie RF630 |
| 24 | 92710041 | Profilo fermapietre - RF630L RF930 | Glazing bead profile - RF630L RF930 | Steinhalteprofil - RF630L RF930 | Profil de blocage des pierres RF630L - RF930 | Perfil sujeción RF630L - RF930 |
| 24 | 92710050 | Profilo fermapietre - RF435 RF635 | Glazing bead profile - RF435 RF635 | Steinhalteprofil - RF435 RF635 | Profil de blocage des pierres RF435 - RF635 | Perfil sujeción pie RF635 |
| 24 | 92710051 | Profilo fermapietre - RF635L RF935 | Glazing bead profile - RF635L RF935 | Steinhalteprofil - RF635L RF935 | Profil de blocage des pierres RF635L - RF935 | Perfil sujeción RF635L - RF935 |
| 26 | 91711220 | Resistenza superiore - RF430 230V 800W | Upper heating element - RF430 230V 800W | Oberer Heizwiderstand RF430 230V 800W | Résistance supérieure - RF430 230V 800W | Resistencia super 230V 800W |
| 26 | 91711221 | Resistenza superiore - RF630 230V 1400W | Upper heating element - RF630 230V 1400W | Oberer Heizwiderstand RF630 230V 1400W | Résistance supérieure - RF630 230V 1400W | Resistencia super 230V 1400W |
| 26 | 91711222 | Resistenza superiore - RF630L 230V 1600W | Upper heating element RF630L 230V 1600W | Oberer Heizwiderstand RF630L 230V 1600W | Résistance supérieure RF630L 230V 1600W | Resistencia super 230V 1600W |

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Description |
|-----|--------------------------|---|--|---|--|------------------------------------|
| 26 | 91711223 | Resistenza superiore - RF930 230V 2000W | Upper heating element - RF930 230V 2000W | Oberer Heizwiderstand RF930 230V 2000W | Résistance supérieure - RF930 230V 2000W | Resistencia superior 230V 2000W |
| 26 | 91711230 | Resistenza superiore - RF435 230V 1000W | Upper heating element - RF435 230V 1000W | Oberer Heizwiderstand RF435 230V 1000W | Résistance supérieure - RF435 230V 1000W | Resistencia superior 230V 1000W |
| 26 | 91711231 | Resistenza superiore - RF635 230V 1600W | Upper heating element - RF635 230V 1600W | Oberer Heizwiderstand RF635 230V 1600W | Résistance supérieure - RF635 230V 1600W | Resistencia superior 230V 1600W |
| 26 | 91711235 | Resistenza superiore - RF635L 230V 2000W | Upper heating element - RF635L 230V 2000W | Oberer Heizwiderstand RF635L 230V 2000W | Résistance supérieure - RF635L 230V 2000W | Resistencia superior 230V 2000W |
| 26 | 91711233 | Resistenza superiore - RF935 230V 2400W | Upper heating element - RF935 230V 2400W | Oberer Heizwiderstand RF935 230V 2400W | Résistance supérieure - RF935 230V 2400W | Resistencia superior 230V 2400W |
| 27 | 91711200 | Resistenza inferiore - RF430 230V 600W | Lower heating element - RF430 230V 600W | Unterer Heizwiderstand RF430 230V 600W | Résistance inférieure - RF430 230V 600W | Resistencia inferior 230V 600W |
| 27 | 91711201 | Resistenza inferiore - RF630 230V 1000W | Lower heating element - RF630 230V 1000W | Unterer Heizwiderstand RF630 230V 1000W | Résistance inférieure - RF630 230V 1000W | Resistencia inferior 230V 1000W |
| 27 | 91711202 | Resistenza inferiore - RF630L 230V 1000W | Lower heating element - RF630L 230V 1000W | Unterer Heizwiderstand RF630L 230V 1000W | Résistance inférieure - RF630L 230V 1000W | Resistencia inferior 230V 1000W |
| 27 | 91711203 | Resistenza inferiore - RF930 230V 1500W | Lower heating element - RF930 230V 1500W | Unterer Heizwiderstand RF930 230V 1500W | Résistance inférieure - RF930 230V 1500W | Resistencia inferior 230V 1500W |
| 27 | 91711210 | Resistenza inferiore - RF435 230V 700W | Lower heating element - RF435 230V 700W | Unterer Heizwiderstand RF435 230V 700W | Résistance inférieure - RF435 230V 700W | Resistencia inferior 230V 700W |

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Descricio |
|---|--------------------------|---|---|---|--|------------------------------------|
| 27 | 91711211 | Resistenza inferiore - RF635 230V 1000W | Lower heating element - RF635 230V 1000W | Unterer Heizwiderstand RF635 230V 1000W | Résistance inférieure - RF635 230V 1000W | Resistencia inferior 230V 1000W |
| 27 | 91711214 | Resistenza inferiore - RF635L 230V 1300W | Lower heating element RF635L 230V 1300W | Unterer Heizwiderstand RF635L 230V 1300W | Résistance inférieure - RF635L 230V 1300W | Resistencia inferior 230V 1300W |
| 27 | 91711213 | Resistenza inferiore - RF935 230V 1500W | Lower heating element - RF935 230V 1500W | Unterer Heizwiderstand RF935 230V 1500W | Résistance inférieure - RF935 230V 1500W | Resistencia inferior 230V 1500W |
| 28 | 91510046 | Pomolo camino | Flue knob | Knauf Dampfablass | Bouton cheminée | Pomo chimenea |
| 29 | 92720190 | Asta camino - RF430 - RF630L | Flue pipe - RF430 - RF630L | Stange Dampfablass - RF430 - RF630L | Tige cheminée - RF430 - RF630L | Barra chimenea RF630L |
| 29 | 92720191 | Asta camino - RF630 - RF930 | Flue pipe - RF630 - RF930 | Stange Dampfablass - RF630 - RF930 | Tige cheminée - RF630 - RF930 | Barra chimenea RF930 |
| 29 | 92720200 | Asta camino - RF435 - RF635L | Flue pipe - RF435 - RF635L | Stange Dampfablass - RF435 - RF635L | Tige cheminée - RF435 - RF635L | Barra chimenea RF635L |
| 29 | 92720201 | Asta camino - RF635 - RF935 | Flue pipe - RF635 - RF935 | Stange Dampfablass - RF635 - RF935 | Tige cheminée - RF635 - RF935 | Barra chimenea RF935 |
| 30 | 92720210 | Scorrevole camino | Sliding flue | Gleitelement Dampfablass | Élément coulissant cheminée | Corredera chimenea |
| 31 | 91310196 | Lampada alogena 12V (*) | Halogen lamp 12V (*) | Halogenlampe 12V (*) | Lampe halogène 12V (*) | Lámpara halógena |
| 31 | 91310206 | Lampada alogena 230V (*) | Halogen lamp 230V (*) | Halogenlampe 230V (*) | Lampe halogène 230V (*) | Lámpara halógena |
| 32 | 91610025 | Vetro portalampada | Glass lamp holder | Leuchtenglas | Verre porte-lampe | Cristal portálampara |
| 33 | 91810185 | Portalampada 12V (**) | Light socket 12V (**) | Glühbirnenhalterung 12V (**) | Porte-lampe 12V (**) | Portálamparas 12V |
| 33 | 91310188 | Portalampada 230V (**) | Light socket 230V (**) | Glühbirnenhalterung 230V (**) | Porte-lampe 230V (**) | Portálamparas 230V |
| (*) 91310206 < 31/03/2012 (s/n 1203 1008) (s/n 1204 1011) 01/04/2012 < 91310196 | | | | | | |
| (**) 91310188 < 31/03/2012 (s/n 1203 1008) (s/n 1204 1011) 01/04/2012 < 91810185 | | | | | | |

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Description |
|-----|--------------------------|------------------------------------|------------------------------------|--------------------------------------|---|---------------------------------|
| 34 | 92710140 | Pannello sx - RF430/1E - RF630L/1E | Left panel - RF430/1E - RF630L/1E | Paneel links - RF430/1E - RF630L/1E | Panneau latéral gauche - RF430/1E - RF630L/1E | Panel lateral izdo. - RF630L/1E |
| 34 | 92710141 | Pannello sx - RF630/1E - RF930/1E | Left panel - RF630/1E - RF930/1E | Paneel links - RF630/1E - RF930/1E | Panneau latéral gauche - RF630/1E - RF930/1E | Panel lateral izdo. - RF930/1E |
| 34 | 92710145 | Pannello sx - RF430/2E - RF630L/2E | Left panel - RF430/2E - RF630L/2E | Paneel links - RF430/2E - RF630L/2E | Panneau latéral gauche - RF430/2E - RF630L/2E | Panel lateral izdo. - RF630L/2E |
| 34 | 92710146 | Pannello sx - RF630/2E - RF930/2E | Left panel - RF630/2E - RF930/2E | Paneel links - RF630/2E - RF930/2E | Panneau latéral gauche - RF630/2E - RF930/2E | Panel lateral izdo. - RF930/2E |
| 34 | 92710150 | Pannello sx - RF435/1E - RF635L/1E | Left panel - RF435/1E - RF635L/1E | Paneel links - RF435/1E - RF635L/1E | Panneau latéral gauche - RF435/1E - RF635L/1E | Panel lateral izdo. - RF635L/1E |
| 34 | 92710151 | Pannello sx - RF635/1E - RF935/1E | Left panel - RF635/1E - RF935/1E | Paneel links - RF635/1E - RF935/1E | Panneau latéral gauche - RF635/1E - RF935/1E | Panel lateral izdo. - RF935/1E |
| 34 | 92710155 | Pannello sx - RF435/2E - RF635L/2E | Left panel - RF435/2E - RF635L/2E | Paneel links - RF435/2E - RF635L/2E | Panneau latéral gauche - RF435/2E - RF635L/2E | Panel lateral izdo. - RF635L/2E |
| 34 | 92710156 | Pannello sx - RF635/2E - RF935/2E | Left panel - RF635/2E - RF935/2E | Paneel links - RF635/2E - RF935/2E | Panneau latéral gauche - RF635/2E - RF935/2E | Panel lateral izdo. - RF935/2E |
| 35 | 92710160 | Pannello dx - RF430/1E - RF630L/1E | Right panel - RF430/1E - RF630L/1E | Paneel rechts - RF430/1E - RF630L/1E | Panneau latéral droit - RF430/1E - RF630L/1E | Panel lateral dcho. - RF630L/1E |
| 35 | 92710161 | Pannello dx - RF630/1E - RF930/1E | Right panel - RF630/1E - RF930/1E | Paneel rechts - RF630/1E - RF930/1E | Panneau latéral droit - RF630/1E - RF930/1E | Panel lateral dcho. - RF930/1E |
| 35 | 92710165 | Pannello dx - RF430/2E - RF630L/2E | Right panel - RF430/2E - RF630L/2E | Paneel rechts - RF430/2E - RF630L/2E | Panneau latéral droit - RF430/2E - RF630L/2E | Panel lateral dcho. - RF630L/2E |
| 35 | 92710166 | Pannello dx - RF630/2E - RF930/2E | Right panel - RF630/2E - RF930/2E | Paneel rechts - RF630/2E - RF930/2E | Panneau latéral droit - RF630/2E - RF930/2E | Panel lateral dcho. - RF930/2E |
| 35 | 92710170 | Pannello dx - RF435/1E - RF635L/1E | Right panel - RF435/1E - RF635L/1E | Paneel rechts - RF435/1E - RF635L/1E | Panneau latéral droit - RF435/1E - RF635L/1E | Panel lateral dcho. - RF635L/1E |
| 35 | 92710171 | Pannello dx - RF635/1E - RF935/1E | Right panel - RF635/1E - RF935/1E | Paneel rechts - RF635/1E - RF935/1E | Panneau latéral droit - RF635/1E - RF935/1E | Panel lateral dcho. - RF935/1E |
| 35 | 92710175 | Pannello dx - RF435/2E - RF635L/2E | Right panel - RF435/2E - RF635L/2E | Paneel rechts - RF435/2E - RF635L/2E | Panneau latéral droit - RF435/2E - RF635L/2E | Panel lateral dcho. - RF635L/2E |
| 35 | 92710176 | Pannello dx - RF635/2E - RF935/2E | Right panel - RF635/2E - RF935/2E | Paneel rechts - RF635/2E - RF935/2E | Panneau latéral droit - RF635/2E - RF935/2E | Panel lateral dcho. - RF935/2E |

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Description |
|-----|--------------------------|-----------------------|-------------------------------|-------------------|----------------------------------|----------------------|
| 36 | 92710080 | Involucro - RF430/1E | Enclosure - RF430/1E | Hülle - RF430/1E | Enveloppe - RF430/1E | Cubierta - RF430/1E |
| 36 | 92710081 | Involucro - RF430/2E | Enclosure - RF430/2E | Hülle - RF430/2E | Enveloppe - RF430/2E | Cubierta - RF430/2E |
| 36 | 92710090 | Involucro - RF630/1E | Enclosure - RF630/1E | Hülle - RF630/1E | Enveloppe - RF630/1E | Cubierta - RF630/1E |
| 36 | 92710091 | Involucro - RF630/2E | Enclosure - RF630/2E | Hülle - RF630/2E | Enveloppe - RF630/2E | Cubierta - RF630/2E |
| 36 | 92710082 | Involucro - RF630L/1E | Enclosure - RF630L/1E | Hülle - RF630L/1E | Enveloppe - RF630L/1E | Cubierta - RF630L/1E |
| | 92710084 | | | | | |
| 36 | 92710082 | Involucro - RF630L/2E | Enclosure - RF630L/2E | Hülle - RF630L/2E | Enveloppe - RF630L/2E | Cubierta - RF630L/2E |
| | 92710094 | | | | | |
| 36 | 92710083 | Involucro - RF930/1E | Enclosure - RF930/1E | Hülle - RF930/1E | Enveloppe - RF930/1E | Cubierta - RF930/1E |
| | 92710084 | | | | | |
| 36 | 92710083 | Involucro - RF930/2E | Enclosure - RF930/2E | Hülle - RF930/2E | Enveloppe - RF930/2E | Cubierta - RF930/2E |
| | 92710094 | | | | | |
| 36 | 92710100 | Involucro - RF435/1E | Enclosure - RF435/1E | Hülle - RF435/1E | Enveloppe - RF435/1E | Cubierta - RF435/1E |
| 36 | 92710110 | Involucro - RF435/2E | Enclosure - RF435/2E | Hülle - RF435/2E | Enveloppe - RF435/2E | Cubierta - RF435/2E |
| 36 | 92710101 | Involucro - RF635/1E | Enclosure - RF635/1E | Hülle - RF635/1E | Enveloppe - RF635/1E | Cubierta - RF635/1E |
| 36 | 92710111 | Involucro - RF635/2E | Enclosure - RF635/2E | Hülle - RF635/2E | Enveloppe - RF635/2E | Cubierta - RF635/2E |
| 36 | 92710102 | Involucro - RF635L/1E | Enclosure - RF635L/1E | Hülle - RF635L/1E | Enveloppe - RF635L/1E | Cubierta - RF635L/1E |
| | 92710104 | | | | | |
| 36 | 92710102 | Involucro - RF635L/2E | Enclosure - RF635L/2E | Hülle - RF635L/2E | Enveloppe - RF635L/2E | Cubierta - RF635L/2E |
| | 92710114 | | | | | |
| 36 | 92710103 | Involucro - RF935/1E | Enclosure - RF935/1E | Hülle - RF935/1E | Enveloppe - RF935/1E | Cubierta - RF935/1E |
| | 92710104 | | | | | |
| 36 | 92710103 | Involucro - RF935/2E | Enclosure - RF935/2E | Hülle - RF935/2E | Enveloppe - RF935/2E | Cubierta - RF935/2E |
| | 92710114 | | | | | |
| 38 | 92810130 | Maniglia inox | Stainless steel handle | Edelstahlgriff | Poignée inox | Asa inox |
| 39 | 91510060 | Rondella salvamani | Flat (hand protection) washer | Handschutzgummi | Rondelle de protection des mains | Arandela protecció |

| Nr. | Codice Code Código | Descrizione | Description | Beschreibung | Description | Description |
|-----|--------------------------|-------------------------------------|-------------------------------------|-------------------------------------|---|--|
| 40 | 91110011 | Vite zincata TCE M8x16 | Zinc-coated TCE M8x16 screws | Schraube verzinkt TCE M8x16 | Vis galvanisée TCE M8x16 | Tornillo galvanizado M8x16 |
| 41 | 92810140 | Rondella porta | Door washer | Unterlegscheibe Tür | Rondelle porte | Arandela de la puerta |
| 42 | 91310320 | Ventola | Fan | Gebälse | Ventilateur | Ventilador |
| 43 | 92720280 | Guarnizione porta - RF430 RF630 | Fibreglass gasket - RF430 RF630 | Glasfaserdichtung - RF430 RF630 | Joint en fibre de verre - RF430 RF630 | Junta en fibra de vidrio - RF630 |
| 43 | 92720281 | Guarnizione porta - RF630L RF930 | Fibreglass gasket - RF630L RF930 | Glasfaserdichtung - RF630L RF930 | Joint en fibre de verre - RF630L - RF930 | Junta en fibra de vidrio - RF630L - RF930 |
| 43 | 92720282 | Guarnizione porta - RF435 RF635 | Fibreglass gasket - RF435 RF635 | Glasfaserdichtung - RF435 RF635 | Joint en fibre de verre - RF435 RF635 | Junta en fibra de vidrio - RF635 |
| 43 | 92720283 | Guarnizione porta - RF635L RF935 | Fibreglass gasket - RF635L RF935 | Glasfaserdichtung - RF635L RF935 | Joint en fibre de verre - RF635L - RF935 | Junta en fibra de vidrio - RF635L - RF935 |
| 44 | 91310356 | Trasformatore 230/12V 50VA | Transformer 230/12V 50VA | Transformator 230/12V 50VA | Transformateur 230/12V 50VA | Transformador 230/12V 50VA |